

The most frequently requested PELT System parts are listed in the following tables. These parts are typically in stock and usually ship within 2-3 business days. Contact your Technical Service Representative or local distributor for pricing and product availability information.

[see- http://Imaginant.com/OrderPELT.html](http://Imaginant.com/OrderPELT.html) for international locations and authorized distributors.)

| <div style="display: flex; justify-content: space-between; align-items: center;"> <div style="flex: 1;"> <p><b>Common Parts</b> (All PELT Product Lines)</p> </div> <div style="flex: 1; text-align: center;">  </div> </div> |              |   |
|---|--------------|---|
| Image   | Part Number  | Description   |
|   | PELT-CAP-STD | Standard 10 mil transducer wear-cap for part number PELT-XER-M (minimum quantity of 5 required)       |
|    | PELT-CAP-SML | Small diameter 10 mil transducer wearcap for part number PELT-XER-SM (minimum quantity of 5 required) |
|    | WC-U1STM15   | Standard 15 mil transducer wearcap (minimum quantity of 5 required)                                   |
|    | WC-U1STU40   | Standard 40 mil transducer wearcap (minimum quantity of 5 required)                                   |
|    | FC-U1STU10   | Standard diameter 10 mil FlexCap (minimum quantity of 5 required)                                     |

|   |                 |   |
|---|-----------------|---|
| <b>Miscellaneous Parts (All PELT Product Lines)</b>                                 |                 |   |
| Image   | Part Number     | Description   |
|    | FC-U1STU20      | Standard diameter 20 mil FlexCap (minimum quantity of 5 required) |
|    | FC-U1STM40      | Standard diameter 40 mil FlexCap (minimum quantity of 5 required) |
|  | PELT-GLY-02     | 2 oz. bottle of glycerin couplant (MSDS included)                 |
|  | PELT-CER-SHM-02 | Certified thickness standard shim for standard transducer         |
|  | PELT-CER-SH-100 | Certified thickness standard shim for 100 MHz transducer          |
|  | PELT-CER-SH-030 | Certified thickness shim for 30 MHz transducer                    |

| <p><b>Common Parts (All PELT Product Lines)</b></p>  |                   |   |
|--|-------------------|---|
| Image  | Part Number       | Description   |
| N/A  | Hold for shim P/N | Certified thickness shim for 10 MHz transducer  |
|   | PELT-XER-M        | Standard transducer 0.34" diameter face (glass delay line)                              |
|   | PELT-XER-SM       | Small transducer 0.26" diameter face (glass delay line)                                 |
|   | PELT-XER-M100     | 100 MHz transducer for high energy PELT gauges - 0.34" diameter face (glass delay line) |
|   | PELT-XER-0100     | 30 MHz transducer for high energy PELT gauges - 0.34" diameter face (glass delay line)  |
| N/A  | PELT-XER-M10      | 10 MHz transducer for high energy PELT gauges (acrylic delay line)                      |

| <b>uPELT-ts Parts</b> (uPts3, uPts3H, uPts5, uPts5+)  |                    |   |
|---|--------------------|---|
| Image   | Part Number        | Description                                   |
|    | PELT-uPts-CBL150   | Transducer cable, SMA connector               |
|    | PELT-uPts-BAT      | uPELT-ts gauge battery, Lithium Ion           |
|    | PELT-uPts-CBLUSB   | USB Cable from uPELT-ts gauge to Windows PC   |
|    | PELT-UP-BATC       | Battery charger for PELT-uPts-BAT01           |
|    | PELT-uPts-EXTPWR   | uPELT-ts gauge external power supply (5V, 3A) |
|    | PELT-uPts-STRPHNDF | uPELT-ts gauge hand strap, full               |

| <b>uPELT-ts Parts (uPts3, uPts3H, uPts5, uPts5+)</b>                              |                    |  |
|---|--------------------|--|
| Image   | Part Number        | Description  |
|  | PELT-uPts-STRPHNDH | uPELT-ts gauge hand strap, half  |
|  | PELT-uPts-STRPNCK  | uPELT-ts gauge neck strap  |

| <b>uPELT Parts (uP301, uP301HE, uP501, UP501A, UP502)</b>                           |                |   |
|---|----------------|---|
| Image   | Part Number    | Description   |
|  | PELT-UP-CBL555 | Right angle SMB 25 ohm cable, 48" in length (model uP501 only)                        |
|  | PELT-UP-CBL450 | Straight BNC 25 ohm cable, 48" in length (model models uP301, uP301HE, uP501A, uP502) |
|  | PELT-UP-ADTAC  | External power supply (models uP301, uP301HE, uP501, uP501A, uP502)                   |

| <b>uPELT Parts (uP301, uP301HE, uP501, UP501A, UP502)</b>  |                    |  |
|--|--------------------|--|
| <b>Image</b>   | <b>Part Number</b> | <b>Description</b>   |
|   | PELT-UP-BAT01      | NiMH battery 3.8 Ah.<br>(models uP301, uP301HE, uP501, uP501A, uP502)    |
|   | PELT-UP-BATC       | Battery charger for part number PELT-UP-BAT01<br>(All uPELT models)      |
|   | PELT-UP-CBLPC1     | Female to male null modem cable<br>(model uP301, uP301HE, uP501A, uP502) |
|   | PELT-UP-CBLPC      | Female to female null modem cable<br>(model uP501 only)                  |
|   | PELT-UP-ADPUSB     | uPELT serial RS-232 to USB adapter cable                                 |